



HEPA-AIRE® PORTABLE AIR SCRUBBER

Lightweight & Compact | Daisy-Chain for More Cleaning Power

PAS750

PAS750

Up to five PAS750 units can be daisy-chained to produce up to 3,750 CFM on a single 15 amp circuit. That gives you the flexibility to add units according to the requirements of the job.

FEATURES & BENEFITS

- Variable speed airflow, with maximum rated airflow as high as 750 CFM
- Anodized aluminum cabinet is lightweight and resistant to corrosion and scratching
- Multiple units nest securely together, to save space when stacked in a warehouse, a van, or in use on the job
- Up to five PAS750 units can be safely daisy-chained on one 15-amp circuit
- Easy-opening swing out hinged door with a secure cam latch and a gasket to protect against filter by-pass
- The PAS750 has been independently tested and certified in accordance with applicable UL and CSA safety requirements



TECHNICAL SPECIFICATIONS

DESCRIPTION	UNIT	PAS750
Net Weight	lbs (kg)	33.5 (15.20)
Dimensions (L x W x H)	in (cm)	23.75 x 18 x 17.5 (60.325 x 45.72 x 44.45)
Electrical Rating	V, Hz, A	120 VAC, 60 Hz, 15 A
Airflow*, Max. w/ Clean Filters	CFM	Variable, 200-750
Normal Operating Amps	A	1.9 or less
Motorized Impeller	-	225 watt, auto reset, 60 Hz, single phase
Sound Level @ 5 Feet	dBA	62-67 on high speed, reading taken at 5'
HEPA Filter Efficiency	-	99.97% @ 0.3 microns
Cabinet Material	-	Anodized aluminum
Prefilter Access	-	Hinged "no tools" access door
First Stage Prefilter	1 ea	F621, 1" deep coarse particulate
Second Stage Prefilter	1 ea	H502, 2" deep pleated particulate
Optional Second Stage	1 ea	VL1002, 2" deep high capacity carbon
HEPA Filter	1 ea	H161606-99

Specifications and details are subject to change without prior notice.



*Note: Airflow ratings estimates are based on factory and independent testing @ 120 VAC with an air straightener and a traverse of readings taken with a computing vane-anemometer. Actual results may vary for various reasons, including motor and blower and HEPA filter tolerances. Factors such as filter loading, reduced voltage to the motor, and inlet and outlet ducting will reduce airflow. Use these ratings as a general guideline only.

CONTACT US FOR MORE INFORMATION

ABATEMENT
TECHNOLOGIES®
LEADERS IN CLEAN AIR

USA
1-800-634-9091
ABATEMENT.COM
IAQINFO@ABATEMENT.COM

CANADA
1-800-827-6443
ABATEMENT.CA
IAQINFO@ABATEMENT.CA

THE PAS750 IS BEST SUITED FOR:



HEALTHCARE CONSTRUCTION



ABATEMENT & REMEDIATION



HEALTHCARE FACILITIES



CRITICAL ENVIRONMENT PROTECTION